

CellID 125

Power system

Description

CellID systems are small, just like cells. They can be embedded in the telecom infrastructure and are often used in OutD outdoor solutions. The products in this series are light and designed especially for installations with limited space offering high density of the installed power.

The system includes high efficiency rectifiers, AC and DC connections, battery connection and either Delta ORION or PSC3 controller. In addition to advanced supervision, short depth and easy installation are the success factors of the system.

Delta is known for quality and product reliability – in this solution that has been combined to optimize the total cost of ownership.

Main features

- 19in rack mounted system up to 8.7 kW
- Integrated 19IN 3U power system
- High efficiency rectifiers up to 96.2 %
- All connections easily accessible from the top
- All battery and load breakers accessible at the front
- Sliding mechanism to support easy access to the output connections
- Option for enhanced monitoring and controlling

Applications

- Wireless applications, network base stations, LTE
- Fixed line applications, broadband services
- Transmission



CellID 125

Power system

Technical specifications

	DPS 1600B-48-4 CellID 125	DPS 2900B-48-3 CellID 125
Rectifier module	DPR 1600B-48 (max. 4 pcs.)	DPR 2900B-48 (max. 3 pcs.)
Efficiency	92 %	96.4 % or 97.2 %
Install power (max. config.)	6.4 kW	8.7 kW
Input current (per 1 phase)	19 A _{RMS} (L1) , 9.5 A _{RMS} (L2&L3)	17 A _{RMS}
Input protection (recom.)	3 x 20 A	3 x 20 A
Height	133.5 mm (3U)	133.5 mm (3U)
Width	481.5 mm (19")	481.5 mm (19")
Depth (overall)	278.5 mm	329 mm
Weight	15 kg	15 kg

AC input	
AC configuration	3L + N + PE or 3 x (L + N + PE) or L+N+PE
Input voltage range	80 ... 300 V _{RMS}
Frequency range	45 – 66 Hz
Mains connection	Cable / Screw terminals
Input protection	N loss, Internal OVP, Inbuilt fuses (L+N), High input voltage

DC output	
Output voltage range	42-58 V _{DC} ; 53.5 V _{DC, nom.}
Output current (max.)	125 A
Load breakers (18 mm)	11 x MCB (DPS 2900B-48-3) 9 x MCB (DPS 1600B-48-4)
Optionally narrow load breakers (13 mm)	15 x MCB (DPS 2900B-48-3) 12 x MCB (DPS 1600B-48-4)
Battery breakers	2 x MCB (80 – 125A)
LVD (battery)	200 A (standard)
PLD (not critical loads)	100 A (option)
Critical / non critical loads configuration (18 mm)	5 x MCB + 4-6 x MCB (depending on rectifier type)
Critical / non critical loads configuration (13 mm)	7 x MCB + 5-8 x MCB (depending on rectifier type)
Output protection	Inbuilt fuses (both poles), High output voltage, Over-temperature protection

Control / Monitoring	
Controller	ORION or PSC 3
Local interface	Display, menu structure, keypads, LEDs
Remote monitoring	6 alarm relays, modems, WEB Interface, SNMP protocol

Others	
Operating temperature	-45 - +65 °C
Humidity (relative)	95 % max, non cond.
Environment standard	ETSI EN 300 019-1-3
Safety standard	IEC 60950
EMC standard	EN 300 386

Ordering	
System	3791605600
Rectifier DPR 1600B-48	TPS1010001B
Rectifier DPR 2900B-48 96.4 %	ESR-48/56B F C-A
Rectifier DPR 2900B-48 97.2 %	ESR-48/56D A-M

Delta Energy Systems (Finland) Oy

Juvan teollisuuskatu 15, FIN-02921 Espoo

Phone: +358 9 849 660, Fax: +358 9 8496 6100

www.deltapowersolutions.com

FS_CellID_125_en.docx / Rev. 03 / RPä